

# QuickLink

Low Voltage System  
Phase Cut Dimming



SAVE UP TO **85%**  
WIRING TIME

halolighting.com

March 8, 2022

## HALO® QuickLink Low Voltage Lighting

Save up to 85% on Install Time!

Halo is pleased to announce the **addition of phase cut dimming control** to the Halo QuickLink low voltage lighting system. Installing canless downlights has never been easier. QuickLink is powered by a single LED remote driver and junction box. Twist-connect up to 8 fixtures to the low voltage cable and see why QuickLink wiring is 85% faster compared to traditional downlighting. QuickLink kits come in size 4" and 6" HLBQL and LTQL-DM.

### Features at a Glance

- Kits include:
  - 72W Remote Power Supply with low voltage CMP cable
  - Fixtures: Choose between 4" or 6" canless HLBQL or LTQL-DM downlights
- Power up to 8 fixtures on 1 driver
- Features QuickLink Connectors for ultra-fast wiring and installation
- 120V input, phase cut dimming to 5%
- Self-healing cable allows for repositioning fixtures
- Fixtures are wet location listed for indoors or outdoor
- Fits in 1/2" to 1-1/4" thick ceilings
- Additional fixtures sold separately



### Installing downlights has never been faster.

QuickLink is a canless low voltage lighting system powered by a single LED remote power supply. Twist-connect up to 8 fixtures to the low voltage cable and see why QuickLink Low Voltage is up to 85% faster compared to traditional downlighting.

**1 POWER SUPPLY & MULTIPLE FIXTURES**

Start with a QuickLink Low Voltage Kit

QuickLink Connector: HALO's fastest way to install downlights

Add individual fixtures if needed (sold separately)

Install almost anywhere

## Ordering Information

### Low Voltage Lighting Kit

Kit includes (1) 72W low voltage remote driver, low voltage CMP cable, (4) downlight fixtures.

Catalog Number	Description	UPC	Watts Per	Max Fixtures
HLBQL4069FS1E-4PK	4" HLB QuickLink Kit, phase cut, 4-pack, 35 ft of low voltage CMP cable	080083190102	7.8W	7
HLBQL6099FS1E-4PK	6" HLB QuickLink Kit, phase cut, 4-pack, 35 ft of low voltage CMP cable	080083190126	12.0W	6
LTQL4069S1EDM-4PK	4" LT-DM QuickLink Kit, phase cut, 4-pack, 40 ft of low voltage CMP cable	080083190140	7.0W	8
LTQL6069S1EDM-4PK	6" LT-DM QuickLink Kit, phase cut, 4-pack, 40 ft of low voltage CMP cable	080083190164	8.1W	8

### Additional Fixtures

**Driver NOT included.** Connect additional fixtures to Low Voltage Lighting Kit.

Catalog Number	Description	UPC	Watts Per
HLBQL4069FS1E	4" HLB QuickLink Kit, phase cut	080083190188	7.8W
HLBQL6099FS1E	6" HLB QuickLink Kit, phase cut	080083190218	12.0W
LTQL4069S1EDM	4" LT-DM QuickLink Kit, phase cut	080083190232	7.0W
LTQL6069S1EDM	6" LT-DM QuickLink Kit, phase cut	080083190256	8.1W



HLBQL4069FS1E



HLBQL6099FS1E




LTQL4069S1EDM



LTQL6069S1EDM

### Accessories

Catalog Number	Description	UPC
HL4RSMF	4" round or square new construction mounting frame	080083876167
HL6RSMF	6" round or square new construction mounting frame	080083876181



HL4RSMF



HL6RSMF

### Selling Tools

Specification sheets, brochure, and installation instructions are available now, refer to the [HALO Recessed website](#). Consult FLASH for pricing and availability. Take advantage of this exciting new product introduction and grow your HALO Recessed sales now.

### See HALO in a whole new light!

#### Glenn Siegel

Marketing & Product  
Management Director

#### Joseph Dimperio

Product & Marketing Manager  
HALO Recessed

#### Michael Lunn

Product & Marketing Manager  
HALO Recessed

